

UV-2C-T Microlog SD

(also available for LED measurement up to 20 W/cm²)

- + extra flat 12.5 mm / .5 inches
- + choice of a combination of two different spectral ranges:
- + UV-A intensity mW/cm² + UV-A dose mJ/cm²
- + UV-B intensity mW/cm² + UV-B dose mJ/cm²
- + UV-C intensity mW/cm² + UV-C dose mJ/cm²
- + UV-V intensity mW/cm² + UV-V dose mJ/cm²
- + Permanent or triggered recording*
- + temperature measuring
- + SD Memory Card
- + graphical and numerical display on a PC
- + re-chargeable accu cell
- + further spectral ranges upon request
- + available up to 20W/cm²
- + available with high speed sampling rate 0.0007s(1400/s)



The **UV-2C-T Microlog SD with SD Memory card** is a self-contained, high quality UV measuring instrument. It is designed to measure, record and display peak UV intensity, UV dosage and temperature in the UV curing process.

It is equipped with a choice of two different UV sensors for the individual measuring of

UV-A 315 – 410 nm
UV-B 280 – 315 nm
UV-C 230 – 280 nm
UV-V 395 – 445 nm
Temp 0 to 230° F / 0 to 110° C

With this choice of two different UV-bands many of the measuring requirements of UV curing applications can be covered. Due to its two different UV sensors and the integrated microprocessor the **UV-2C-T Microlog SD with SD Memory card** can measure, record and display the peak of the UV-intensity (mW/cm²) for each UV-band individually plus the peak of total UV energy.

Additionally, this UV-Integrator is calculating the UV-dosage (mJ/cm²) of the UV energy supplied during the time of exposure of one measuring cycle. The UV-dosage is calculated for each UV-band individually.

This allows to determine not only the total energy, but also how that energy is delivered, i.e., what intensity and dose at what UV-band.

An optionally available extra sensor measures temperatures from 0 to 230° F / 0 to 110° C

*The **UV-2C-T Microlog SD with SD Memory card** features a selectable „triggered mode“, i.e. the recording of the measuring starts first if the incident UV-intensity exceeds 2 mW/cm².

The sensors are on the back of the unit which also serves as a heat shield. After completion of the measuring cycle all measuring results can be scrolled through on the built in 2 x 16 digit LCD display.

A special AUTO-OFF feature that turns off the unit automatically after one minute serves as energy saving and extension of the battery service life.

This microprocessor integrator is additionally equipped with a Card Slot for the use of SD-Memory Cards. All measuring data of a measuring cycle are stored to the SD-Memory card with an identifying file name. The number of storable measuring files depends on the capacity of SD-Memory Card. Data can be loaded to a PC for further editing. The special evaluation software allows to show, edit and store a history of the measuring results of the entire measuring cycle as graphic charts (mW/cm²) and (mJ/cm²) and (°C/°F)

- | | | |
|-----------------------------|------|----------------|
| 18.6.1. UV-2C-T Microlog SD | UV-A | + UV-V + Temp. |
| 18.6.2. UV-2C-T Microlog SD | UV-A | + UV-B + Temp. |
| 18.6.3. UV-2C-T Microlog SD | UV | + UV-A + Temp. |
| 18.6.4. UV-2C-T Microlog SD | UV | + UV-B + Temp. |
| 18.6.5. UV-2C-T Microlog SD | UV | + UV-V + Temp. |
| 18.6.6. UV-2C-T Microlog SD | UV-B | + UV-V + Temp. |
| 18.6.7. UV-2C-T Microlog SD | UV-C | + UV-V + Temp. |
| 18.6.8. UV-2C-T Microlog SD | UV-C | + UV-A + Temp. |

*also available in other spectral range combinations upon request

Subject to change without prior notice © 2014-01

UV-DESIGN (Office)
Triebstrasse 3
63636 Brachtal
GERMANY
Tel.: +49 (0)6053 619824
Fax: +49 (0)6053 619820

(Office & Workshop) UV-DESIGN
Fabrikstrasse 12
63636 Brachtal
GERMANY
Tel.: +49 (0)6053 8095431
Fax: +49 (0)6053 8095433



UV-2C-T Microlog SD

Technical Data:

Spectral ranges: (available choice)	UV-A 315 – 410 nm UV-B 280 – 315 nm UV-C 230 – 280 nm UV-V 395 – 445 nm UV 230 – 410 nm
Temperature range:	32 to 230° F / 0 to 115° C
Max. Power Input*:	0 to 2,000 mW/cm ²
Measuring range:	0 to 2,000 mW/cm ²
Sampling rate:	0.01 sec (100/sec)
Recording cycle:	90 sec.
Readiness phase:	120 sec.
Display range:	0 to 36,000 mJ/cm ²
Display:	LCD, 2 x 16 digits
Power source:	3.7 V accu cell
Power consumption:	40 µA
Battery service life:	approx. 500 measurements
Dimensions:	140 x 65 x 12 mm (5.5 x 2.4 x 0.5")
Weight:	approx. 8 ounce (250 g)
Operating temperature:	32° to 113° F / 0 to 45° C
Heat protection:	Heat shield on back plate
Base Accuracy:	± 5 %

Graphic Chart:

With SD Card slot.
Stores data to an
SD-Memory card
For transmission to
a computer



While on the conveyer belt, the UV-2C-T Microlog SD can withstand max. 230° F / 110° C for up to 10 seconds. The temperature of the housing should not exceed 113° F / 45° C.

Because of uneven radiation distribution of the UV light source and different type of construction of the measuring devices by different manufacturers, different readings may appear under the same measurement conditions.

Calibration:

In order to keep its full function and precision it is recommended to have re-calibration done once per year. Re-calibration will also be necessary after change of battery. Ongoing, PTB traceable calibration with certificate

*also available up to 20 W/cm², display resolution in relation to maximum power input

*also available with high-speed sampling rate 0.0007 (1400/sec)

Subject to change without prior notice © 2014-01

UV-DESIGN (Office)
Triebstrasse 3
63636 Brachtal
GERMANY
Tel.: +49 (0)6053 619824
Fax: +49 (0)6053 619820

(Office & Workshop) UV-DESIGN
Fabrikstrasse 12
63636 Brachtal
GERMANY
Tel.: +49 (0)6053 8095431
Fax: +49 (0)6053 8095433