

UV-1000 Colour RE UV-MC


- + Available in the following UV ranges
- + UV-A intensity mW/cm² + UV-A dose mJ/cm²
- + UV-B intensity mW/cm² + UV-B dose mJ/cm²
- + UV-C intensity mW/cm² + UV-C dose mJ/cm²
- + UV-V intensity mW/cm² + UV-V dose mJ/cm²
- + Full UV intensity mW/cm2 + Full UV dose mJ/cm2
- + big colour graphic display
- + numerical and graphical display
- + permanent or "triggered" measuring mode*
- + SD Memory Card (option)
- + real-time clock
- + graphic chart on computer (option)
- + re-chargeable accu cells with charger



The **UV-1000 Colour RE Radiometer + Dosimeter** is a self-contained, high quality UV measuring instrument. It is designed to measure and record UV intensity and UV dosage in the UV curing process. Measuring results are indicated both, graphically and numerically on a big colour display.

It is equipped with one UV sensors for the individual measuring of either:

UV-A	315 – 410 nm
UV-B	280 – 315 nm
UV-C	230 – 280 nm
UV-V	395 – 445 nm
Full UV	230 – 410 nm



Due to its UV sensors and the integrated microprocessor the *UV-1000 Colour RE Radiometer* + *Dosimeter* can measure, record and display the peak of the UV-intensity (mW/cm²) plus the peak of total UV energy.

Additionally, this instrument is calculating the UV-dosage (mJ/cm²) of the UV energy supplied during the time of exposure of one measuring cycle. The UV-dosage is calculated as total Integral of UV-dosage over the respective UV-range. This allows to determine not only the total energy, but also how that energy is delivered, i.e., what intensity and dose at what UV-band.

Optionally, an extra sensor measures temperature in °C/°F

*This instrument features a selectable "triggered mode", i.e. the 30 sec recording cycle starts within a 120 second readiness phase not before the incident UV-intensity exceeds 2 mW/cm².

The sensor is on the back of the unit which also serves as a heat shield. After completion of the measuring cycle the measuring results are instantly displayed numerically and graphically auto-scaled on the built in 45 x 34 mm (2 1/2") TFT colour display.

A special AUTO-OFF feature that turns off the unit automatically after one minute serves as energy saving and extension of the battery service life.

This Radiometer + Dosimeter can optionally be equipped with an SD-Memory Card Slot and an evaluation software for downloading the data to a computer to show, edit and store a history of the measuring results of the entire measuring cycle as graphic charts (mW/cm2) and (mJ/cm2)

64.1.1 UV-1001 Colour RE UV-MC, Diazo 350 – 460 nm 64.1.2 UV-1002 Colour RE UV-MC, UV-A 315 – 400 nm

64.1.3 UV-1003 Colour RE UV-MC, UV 250 – 410 nm (Standard)

64.1.4 UV-1004 Colour RE UV-MC, UV-B 280 – 315 nm 64.1.5 UV-1005 Colour RE UV-MC, UV-C 230 – 280 nm 64.1.6 UV-1006 Colour RE UV-MC, UV-V 395 – 445 nm

Subject to change without prior notice © 2014-01

UV-DESIGN (Office) Triebstrasse 3 63636 Brachttal GERMANY Tel.: +49 (0)6053 619824 Fax: +49 (0)6053 619820 (Office & Workshop) UV-DESIGN Fabrikstrasse 12 63636 Brachttal GERMANY Tel.: +49 (0)6053 8095431 Fax: +49 (0)6053 8095433



UV-1000 Colour RE UV-MC

Technical Data:

Available spectral ranges: UV-A 315 – 410 nm

UV-B 280 – 315 nm UV-C 230 – 280 nm UV-V 395 – 445 nm Full UV 230 – 410 nm

Max. Power Input 0 to 5,000 mW/cm²

Measuring range: 0 to 2,000 mW/cm²

Sampling rate: 0.02 sec (50/sec)

Recording cycle: 30 sec.

Readiness phase: 120 sec.

Display range: 0 to 36,000 mJ/cm²

Display: TFT Colour Display, 45 x 34 mm (2 1/2")

Power source: 3.7 V LiPO Accu

Power consumption: 80 µA

Accu service life: 1,000 re-charging cycles

Dimensions: approx. 4" x 6.5" (105 x 165 mm), height .55" (14 mm)

Weight: approx. 17.5 ounce (500 g)


Operating temperature: 32° to 113° F / 0 to 45° Celsius


Heat protection: Heat shield on back plate

Base Accuracy: ± 5 %




Stores data on SD-Memory Card for the download of data to a Computer





Option: Graphical display on PC



While on the conveyer belt, the *UV-1000 Colour RE Radiometer* + *Dosimeter* can withstand max. 230° F / 110° C for up to 10 seconds. The temperature of the housing should not exceed 113° F / 45° C. Because of uneven radiation distribution of the UV light source and different type of construction of the measuring devices by different manufacturers, different readings may appear under the same measurement conditions.

Calibration:

In order to keep its full function and precision it is recommended to have re-calibration done once per year. Re-calibration will also be necessary after change of battery. PTB traceable calibration with certificate

Subject to change without prior notice © 2014-01

UV-DESIGN (Office) Triebstrasse 3 63636 Brachttal GERMANY

Tel.: +49 (0)6053 619824 Fax: +49 (0)6053 619820 (Office & Workshop) UV-DESIGN Fabrikstrasse 12 63636 Brachttal GERMANY Tel.: +49 (0)6053 8095431 Fax: +49 (0)6053 8095433